



Electronics

a vital part of your world

Find Answers:

Saturday, 15 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Soft Shell Connectors

↳ Soft Shell - Accessories

AMP 641763-1 Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Corporate P/N: 641763-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ▾ General Info ▾ Sales Info ▾ Assembly Subcontractors 	<ul style="list-style-type: none"> ▾ Pricing ▾ Product Availability 	<ul style="list-style-type: none"> ▾ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Strain Relief
Connector Line:	Universal MATE-N-LOK
Housing Material:	Nylon
Color:	Natural
Number of Circuits:	3
Contact Layout:	In-Line
Insert Supplied:	No
Flammability Rating:	UL 94V-2

Other Properties:	
RoHS/ELV Compliance History:	Always was RoHS compliant
Wire Diameter Range (mm [in]):	5.08 – 8.89 [0.200 – 0.350]
Comment:	Strain relief part number represents one half of a strain relief. Two of a part number are required per connector. Must use cap housing adapters when attaching strain reliefs to a cap housing. Two adapters required per housing.

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

